



# YUKON Split System Air Conditioner

Tall Floor Type 36,000-120,000 Btu/h MCV Series 50/60 Hz



### **YUKON**-Human Comfort Solution





#### **Comfort and Reliability**

- Full Range of Capacity
- Energy Savings
- · Washable Filter
- · Low Maintenance
- · Easy to Service
- · Lower Noise

#### Quality

All major components are individually inspected and tested, and every unit undergoes a run- test prior to shipment from the factory.

#### **High Efficiency**

- Compact in size for easy installation into small spaces
- Galvanized steel with a powder paint finish for corrosion resistance
- Synchronus motor for supply grille as standard for better airflow

#### **Serviceability**

The unit can be easily serviced and minimum area required just only at the front after panel.

Trane is proud to present its complete line of Tall Floor split system air conditioners with modern design. This system has been not only carefully designed and manufactured according to Trane Worldwide Quality Standards but also luxuriously designed to provide you with years of comfortable, convinient cooling with minimal service required and also easy to service.

The benefits of a system have been extended to a broader range of full cooling capacity, making Yukon the perfect to your new or replacement application.



## Digital Control



#### **Digital Control**

With microprocessor and digital technology, Yukon provides accurate room temperature control with a numerical temperature display.

#### **Power**

The power button is used to turn the air conditioner on and off operating according to the last program stored in the non-volatile memory.

The display unit will show:

- · Room temperature in degrees celcius
- · Fan speed

#### **Temperature**

The TEMP + and - buttons are used to adjust the set temperature from  $15\,^{\circ}\text{C}$  to  $30\,^{\circ}\text{C}$ . When the button is pressed, the control unit will display the set temperature (blinking) instead of the room temperature. After the process is finished, it will revert back to the room temperature.

#### Fan

Fan speed (Auto, High, Medium, or Low) can be selected by pressing the FAN button.

#### **Auto Fan**

Fan speed can be put in the AUTO mode so that the fan speed will change automatically depending on the difference between the room and set temperatures.

If the difference is large, it will operate at high speed



for faster cooling. As the smaller, the fan speed will be changed automatically to Medium and then Low as indicated by the position of the fan speed LED indicator.

#### **Time Delay**

A 3-minute time delay protects against power interruptions and rapid compressor cycling which could damage the air conditioning unit.

#### Freeze protection

The freeze protection function will protect coil from freezing by turning off the compressor.

#### Swing

The auto vertical vane swing can be selected by pressing the SWING button.



Condensing Unit TTK536-042



Condensing Unit TTK 048-060



Condensing Unit TTA 075-120

#### Product Specifications: 50 Hz

Model	Indoor Unit		MCV036BB	MCV036BB	MCV048BB	MCV048BB	MCV060BB	MCV090BB	MCV090BB	MCV120BB	
	Outdoor Unit		TTK536KB	TTK536KD	TTK042KD	TTK048KD	TTK060KD	TTA075RD	TTA100RD	TTA120RD	
Electrical Data	Power Supply	V/ph/Hz	220-240/1/50 380-415/3/50							•	
Performance Data	Nominal Capacity	Btu/h	36,000	36,000	42,000	48,000	60,000	75,000	90,000	120,000	
	Nominal Airflow	cfm	1,200	1,200	1,400	1,600	2,000	2,400	2,400	3,200	
Indoor Unit						•					
Expansion Device			Capillary Tube				Expansion Device				
Fan Motor	Туре		Permanent Split Capacitor					•			
	RLA/LRA	А	1.78/1.97	1.78/1.97	2.34/2.74	2.34/2.74	3.42/3.90	(1.78/1.97)x2	(1.78/1.97)x2	(2.34/2.74)x2	
Control Type	Digital Thermostat						•				
Features	3-Minute Time Delay										
	Fan Speed		3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	
	Auto Swing (Vertical Vane)										
	Temperature Setting	°C	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	
	Programmable Timer	Hrs	15	15	15	15	15	15	15	15	
Installed Position	Floor										
Dimension	Height	mm	1,900	1,900	1,900	1,900	1,900	1,900	1,900	1,900	
	Width	mm	600	600	600	600	848	1,196	1,196	1,196	
	Depth	mm	370	370	370	370	400	400	400	400	
Weight		kg	65	65	68	68	90	137	137	144	
Outdoor Unit											
Compressor	Туре		Rot	Rotary			Sc	Scroll			
	RLA\LRA		15.8 / 79.0	5.8 / 43.0	10.0/59.0	10.0/59.0	10.0/74.0	13.6/98.0	20.7/130.0	22.9/145.0	
Fan Motor	Type		Permanent Split Capacitor								
	RLA\LRA		1.03/1.79	1.03/1.79	1.03/1.79	(0.88/1.79) x2	(0.88/1.79) x2	1.06/2.27	1.41/3.53	1.32/2.80	
Dimension	Height	mm	795	795	795	1,254	1,254	1,050	1,050	1,050	
	Width	mm	1,018	1,018	1,018	988	988	950	950	950	
	Depth	mm	360	360	360	350	350	1,060	1,060	1,060	
Weight		kg	79	79	88	92	95	164	180	192	
Piping Connection Type			Flare	Туре			Swea	at Type			
Refrigerant Pipe Size	Liquid	in	3/8	3/8	3/8	3/8	3/8	1/2	1/2	1/2	
	Suction	in	3/4	3/4	7/8	1 1/8	1 1/8	1 1/8	1 3/8	1 3/8	

#### Product Specifications: 60 Hz

Model	Indoor Unit		MCV036B1	MCV048B1	MCV048B1	MCV060B1	MCV060B1	MCV090B1	MCV090B1	MCV120B1
	Outdoor Unit		TTK536K1	TTK042K1	TTK048K1	TTK060K1	TTK060K3	TTA075R3	TTA100R3	TTA120R3
Electrical Data	Power Supply	V/ph/Hz	230/1/60 230/3/60						3/60	
Performance Data	Nominal Capacity	Btu/h	36,000	42,000	48,000	60,000	60,000	75,000	90,000	120,000
	Nominal Airflow	cfm	1,200	1,400	1,600	2,000	2,000	2,400	2,400	3,200
Indoor Unit	•				•			•		
Expansion Device			Capillary Tube Expansion Device						2	
Fan Motor	Type		Permanent Split Capacitor							
	RLA/LRA	A	1.60/1.84	2.20/2.53	2.20/2.53	2.40/2.76	2.40/2.76	(1.60/1.84) x2	(1.60/1.84) x2	(2.20/2.53) x2
Control Type	Digital Thermostat		•		•	•	•	•	•	
Features	3-Minute Time Delay		•			•	•	•		
	Fan Speed		3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto	3 + Auto
	Auto Swing (Vertical Vane)		•		•	•	•	•	•	•
	Temperature Setting	°C	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30	15 - 30
	Programmable Timer	Hrs	15	15	15	15	15	15	15	15
Installed Position	Floor		•		•	•	•	•		•
Dimension	Height	mm	1,900	1,900	1,900	1,900	1,900	1,900	1,900	1,900
	Width	mm	600	600	600	848	848	1,196	1,196	1,196
	Depth	mm	370	370	370	400	400	400	400	400
Weight		kg	65	68	68	90	90	137	137	144
Outdoor Unit										
Compressor	Туре		Scroll							
	RLA\LRA		18.4/95.0	24.3/131.0	24.3/131.0	30.1/175.0	20.7/128.0	25.0/164.0	33.6/231.0	42.0/239.0
Fan Motor	Type		Permanent Split Capacitor							
	RLA\LRA		1.25/1.53	1.25/1.53	(0.66/0.80) x2	(0.66/0.80) x2	(0.66/0.80) x2	2.00/3.03	2.00/3.03	2.59/5.50
Dimension	Height	mm	795	795	1,254	1,254	1,254	1,050	1,050	1,050
	Width	mm	1,018	1,018	988	988	988	950	950	950
	Depth	mm	360	360	350	350	350	1,060	1,060	1,060
Weight		kg	82	84	84	88	88	164	180	192
Piping Connection Type			Flare Type Sweat Type							
Refrigerant Pipe Size	Liquid	in	3/8	3/8	3/8	3/8	3/8	1/2	1/2	1/2
	Suction	in	3/4	7/8	1 1/8	1 1/8	1 1/8	1 1/8	1 3/8	1 3/8

<sup>1.</sup> At ARI system rating conditions of 80°F - DB / 67°F - WB Indoor & 95°F - DB Outdoor.

Rated for 25 feet (7.5 meters) of evacuated refrigerant piping.
 Outdoor unit's dimensions exclude the size of the mounting feet. For more detail, please see the drawing in the installation manual.



Ingersoll Rand (NYSE:IR) is a world leader in creating and sustaining safe, comfortable and efficient environments in commercial, residential and industrial markets. Our people and our family of brands—including Club Car®, Hussmann®, Ingersoll Rand®, Schlage®, Thermo King® and Trane®—work together to enhance the quality and comfort of air in homes and buildings, transport and protect food and perishables, secure homes and commercial properties, and increase industrial productivity and efficiency. We are a \$13 billion global business committed to sustainable business practices within our company and for our customers.

Trane has a policy of continuous product and product data improvement and reserves the right to change design and specifications without notice. Trane Thailand, 999/1 Mu 9, Bangna-Trad km. 19 Rd., Bangchalong, Bangplee, Samutprakarn, Thailand



<sup>1.</sup> At ARI system rating conditions of 80°F - DB / 67°F - WB Indoor & 95°F - DB Outdoor.
2. Rated for 25 feet (7.5 meters) of evacuated refrigerant piping.
3. Outdoor unit's dimensions exclude the size of the mounting feet. For more detail, please see the drawing in the installation manual.